

CT156

WIRELESS PUSH BUTTON STATION Instant Audio/Visual Alerts

Simple Operation, User-Programmable Alerts, Easy Installation

The CT156 Push Button Nurse Call station is a compact, wireless, wall-mounted transmitter that can instantly alert caregivers or staff members when help is needed. The CT156 is designed to function as a standalone device or as part of a Visiplex's paging base station. When used in a standalone configuration, the CT156 can directly send a detailed text message to caregiver pager or a central LED message board, activate beacon or corridor lights to help identify the call's origin, or activate pre-programmed voice messages through wireless PA speakers. When operating as part of a paging base station, the CT156 can in addition to the above, send SMS text message to staff member cell phone, activate 2-way intercom voice communication between the patient room and the main office, and provide full supervision capabilities to ensure reliable operation at all times.

Equipped with a built-in, long lasting Lithium battery, the CT156 will provide years of maintenance-free operation, while offering wireless functionality supervision.



CT156 KEY FEATURES



AUDIO ALERTS
Activate PA Messages



VISUAL ALERTS
Control Beacon Lights and LED Message Boards



ALERTS ANYWHERE
Detailed Phone or Pager Text Alerts



LONG RANGE
Up to 300' Range



FULLY SUPERVISED
Periodic Status Alerts to Monitoring Base Station



LOW MAINTENANCE
Long-Life Lithium Battery



VISIPILEX


1287 BARCLAY BLVD
BUFFALO GROVE, IL 60089

PHONE: 877-918-7243

FAX: 847-229-0259

EMAIL: INFO@VISIPILEX.COM

WEB: WWW.VISIPILEX.COM



CT156 SPECIFICATIONS

Parameter	Description
Color	Off-white body, Off-white push-button cord with red button
Frequency Band	UHF 402-470 MHz
Range	300'
Dimensions	2.75" x 4.5" x 2.1", 70mm x 114mm x 53mm (W x H x D); Cord Length: 7', 2.1m
Weight	9.6oz, 272g
Power	Single CR2 3V Lithium battery
Operating Conditions	Temperature 10°-130°, Humidity 0-90% non-condensing
RF Power	10 mW
Programming	PC Based programming
Mounting Options	In-wall or surface mounting, fits one-gang electrical box
Signalling Time	2-4 Seconds
Stability	Better than 5 PPM
Paging Format	POCSAG, 512, 1200 or 2400 BPS
Channel Spacing	12.5 KHz - Narrow Band
Activation Codes	Call, Cancel & Low Battery
Options	WPA-1003 (Deep Electrical Box), WPA-1025 (Programming Cable)
Warranty	One Year Limited Warranty



VISIPLEX

1287 BARCLAY BLVD
BUFFALO GROVE, IL 60089

PHONE: 877-918-7243

FAX: 847-229-0259

EMAIL: INFO@VISIPLEX.COM

WEB: WWW.VISIPLEX.COM